

# EZ PURGE®

Pre-Formed, Self Adhesive Water Soluble Purge Dams

Revolutionizing the Way TIG Purging is Done

## EZ to use as 1-2-3!

Peel.

1

Peel liner to expose adhesive.



Insert.

2

Insert EZ Purge® dam inside pipe.



To facilitate easy insertion, the side walls of EZ Purge® are tapered to fit different pipe schedules.

Press.

3

Press tape along circumference of pipe wall.



All EZ Purge® come with a generous portion of water soluble tape pre-installed in sections to allow for care free alignment and tacking.

FEATURING

ZAP

TECHNOLOGY

Zero Air Permeability for

Maximum Gas Retention

EPA APPROVED

CE APPROVED



**Your purge dam is complete in minutes!**

**Don't waste labor hours on preparation:**

- Gathering Supplies
- Constructing
- Measuring
- Fitting
- Cutting

**When you can:**

- Peel, Insert & Press
- Start Welding Faster
- Save Time on Labor
- Save Gas
- Get ahead of schedule

# EZ PURGE®

Aquasol  
CORPORATION

Made of Aquasol® Water Soluble Paper and other water soluble polymeric composites and laminates, EZ Purge® dissolves instantaneously and completely in most liquids and is 100% biodegradable.

The shape of EZ Purge® is flat, similar to a mechanical device, to allow equal distribution of gases across the body of the dam. Conical shaped dams force pressure into the tip point, resulting in unnecessary purge failures.



## Available in a variety of sizes!

Item Number	Pipe Diameter	Case Pack (Qty)
EZP-2	2" (51 mm)	192
EZP-3	3" (76 mm)	192
<b>EZP-4</b>	<b>4" (102 mm)</b>	<b>48</b>
EZP-5	5" (127 mm)	48
<b>EZP-6</b>	<b>6" (152 mm)</b>	<b>48</b>
<b>EZP-8</b>	<b>8" (203 mm)</b>	<b>48</b>
EZP-10	10" (254 mm)	48
EZP-12	12" (305 mm)	48
EZP-14	14" (356 mm)	24
EZP-16	16" (406 mm)	24
EZP-18	18" (457 mm)	24
EZP-20	20" (508 mm)	24
EZP-22	22" (559 mm)	24
EZP-24	24" (610 mm)	24
EZP-28	28" (711 mm)	24
EZP-30	30" (762 mm)	24
EZP-32	32" (812 mm)	24
EZP-36	36" (914 mm)	24
EZP-40	40" (1016 mm)	10
EZP-42	42" (1067 mm)	10
EZP-44	44" (1117 mm)	10
EZP-48	48" (1219 mm)	10
EZP-52	52" (1320 mm)	10
EZP-56	56" (1422 mm)	10
EZP-64	64" (1626 mm)	10
EZP-72	72" (1829 mm)	10
EZP-84	84" (2134 mm)	10



### Maximizing Seal

Moisten an ordinary sponge in water. Squeeze excess water out of sponge to avoid dissolving dam.



Lightly dab sponge along the water soluble tape portion of the dam to increase dam adhesion and ensure zero air permeability.



Continue to dab across entire circumference.

*For additional product information, quotations and ordering, please contact:*

Aquasol Corporation  
80 Thompson Street  
North Tonawanda, NY 14120  
Toll Free: 800.564.WELD(9353)  
Phone: 716.564.8888  
Fax: 716.564.8889  
www.aquasolcorporation.com



Made in the U.S.A.

U.S. Patented and Foreign Patents Pending

EZPB3.1111.r.2

*Distributed By:*



**American Welding Society**  
Sustaining Company Member